


Autoclave and Steam Sterilizer Controllers

Steam Sterilizer / Autoclave Controller, Model : **Solo**

- Display: Temperature and Humidity Safe - Functional Numeric Display (FND)
- Control : ON/OFF / T.P.
- Input : PT-100
- Purging Range : User Settable
- Sterilization Time : User Settable
- Post Sterilization-Drying Time : User Settable
- Pressure Display : Pre-Enable (Without Transmitter)
- Buzzer : High / Low Alarm / Process End
- Low Water Sensor Built In
- Two Built in program and access key
- Bowie & Dick Equipment control



Solenoid Valve Control 2 & 3 Nos.




Steam Sterilizer / Autoclave Controller, Model : **Budget**




- Display: Temperature and Humidity Safe - Functional Numeric Display (FND)
- Control : ON/OFF / T.P.
- Input : PT-100
- Purging Range : User Settable
- Sterilization Time : User Settable
- Post Sterilization-Drying Time : User Settable
- Buzzer : High / Low Alarm / Process End

- Low Water Sensor Built In
- Two Built in program and access key
- Bowie & Dick Equipment control



Autoclave / Steam Sterilizer Controller, Model : **Eco Super**

L160mm x W:146mm x H:50mm




No Pressure Sensor AI Based Pressure Display

Solenoid Valve Control 3 & 4 Nos.


Single PT-100 for Chamber and Boiler Control

- Display: Jumbo LCD 20x 4
- Control: ON/OFF / T.P.
- LED Indication for Output Status Indication
- Input: PT-100
- Purging Range : User Settable
- Sterilization Time : User Settable
- Buzzer: High / Low Alarm/Process End
- Pressure Display : Pre-Enable (Without Transmitter)
- Low Water Sensor Built In
- Two Built in Program and Access Key
- Bowie & Dick Equipment Control



Advance Venturi System Vacuum Control

Steam Sterilizer Controller, Model : **Grand** Two PT-100 Sensor | One Pressure Sensor



- Display: Jumbo LCD 20x 4
- Control: ON/OFF / T.P.
- Input: PT-100 for Boiler and chamber, Pressure Sensor for chamber
- Purging Range : User Settable
- Sterilization Time : User Settable
- Post Sterilization-Drying Time : User Settable
- Inlet for HEPA Filter
- Boiler Control: User Settable
- Buzzer: High / Low Alarm/Process End
- Pressure Display with Transmitter
- Sterilization cycle process inbuilt
- Low Water Sensor Built In
- Two Built in program and access key
- Bowie & Dick Equipment control
- Vacuum Pump Control



L:200 mm X W:197mm x D:50mm

Solenoid Valve Control 3, 4, 5 & 6Nos